



### SF7717 and SF7717D Locking Type Call Cords



Model **SF7717** Single Call Cord Shown

#### ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

The call cord(s) shall be Alpha Communications® model **SF7717** (single) or **SF7717D** (double) or approved equal. Model **SF7717** shall provide for a single locking call button. Model **SF7717D** shall provide a 'Y' type cord with two locking call buttons.

The call cord(s) shall be encased in a molded, shockproof plastic case. The **SF7717** shall be provided with a 7' polyvinyl cord. The **SF7717D** shall be provided with dual 7' polyvinyl cords. Call cord(s) shall feature a right-angle molded plug assembly and shall be grey in color. A model **HW155** bed sheet clip shall be supplied (optionally) for each bed location.

Contractor shall observe all local and national electrical and building codes.

#### SF7717 AND SF7717D LOCKING TYPE CALL CORDS

The Alpha Communications® **SF7717** (single) or **SF7717D** (double) locking call cords are designed to be used with a variety of Nurse-Call Systems, on bed stations utilizing 1/4" phono jacks, requiring locking calls that can only be reset at the calling cord, for non UL applications.

The **SF7717** cord features a 7 foot long cord, and the **SF7717D** features twin 7 foot cord lengths. A wide variety of optional call cords are also available for specialty applications such as oxygen tents, geriatric use, and air-call. Contact Alpha Communications® for more information on other call cords available.

#### FEATURES

- Simple Push-button Operation and Oversized Button
- S.P.S.T. 1-Amp Momentary Switch
- Integral brass, hard gold contacts
- Rugged and Reliable.
- Dirt and dust protection
- Must Be Reset at Calling Cord Location by Pulling on Cap
- Bed sheet clips available (Model **HW155**)
- 500 mA, 50-watt maximum, AC

#### SPECIFICATIONS

<b>Construction:</b>	Cord shall be made from a heavy duty grey polyvinyl covered cord with molded right angle plug and locking button.
<b>Push Button:</b>	Locking S.P.S.T. type with integral brass, hard gold contacts, molded into a comfortable "oversized" hand pendant and button cap.
<b>Other Models:</b>	<b>SF7717/10</b> (10 foot cord); <b>SF7717/15</b> (15 foot cord)

#### CALL CORD OPERATION

The patient, by pressing the locking button on the **SF7717** (or **SF7717D**) call cord shall signal for assistance. The actual call signaling functions depend upon which system the call cord is being used with.

#### Alpha Communications

42 Central Drive • Farmingdale • NY • 11735-1202 • Phone: (631) 777-5500 • Fax: (631) 777-5599  
 TOLL-FREE: (800) 666-4800 • Web: [www.alphacommunications.com](http://www.alphacommunications.com) • Email: [info@alphacommunications.com](mailto:info@alphacommunications.com)