

Wet Noodle™

Magnetic In-Wall Retrieval System

Accept no inferior knock-offs. Use the ORIGINAL Wet Noodle Retriever System. LSDI developed the ball chain and magnetic retriever concept many years ago to help save installation time. Since its conception, it immediately became a “must have” tool for retrofit installations. Thanks to our customer’s valuable feedback, LSDI has improved upon the Wet Noodle Retrieval System (WNRS) to provide more versatility and functionality. One significant improvement made to the 24” flexible retriever is the addition of a larger more powerful magnet (1/4”) on the end opposite the original 3/16” Neodymium magnet. Rounding out this useful tool system is 10 feet of lightweight ball chain with stop ring and the addition of our 18” telescoping pocked retriever (LBS).

How to use the Wet Noodle

Create a small hole for an entry point up on the wall (the Wet Noodle works best in uninsulated walls) and drill a small hole at the bottom directly below (1/4”) hole for the small magnet end or 3/8” for the bigger end). Drop the Wet Noodle ball chain down giving it a slight jiggle to make sure it finds the bottom plate. In most cases you will “catch” the ball chain by just putting the magnet end(s) into the bottom hole. If necessary, bend the flexible retriever

into an “S” shape to get into the wall for more difficult retrievals. Slowly pull the ball chain to just inside the bottom hole. Using the pocket retriever, hook the ball chain and bring it out the bottom hole.

The tool kit provides a quick and easy solution for in-wall blind wire pulling making it truly indispensable.



DESCRIPTION	PART NO.	MODEL
Wet Noodle and Retrieval System	LS-85-124	WNRS
10 ft. Ball Chain with Stop Ring and Connectors	LS-85-024	WN10
1,000 ft. Roll Ball Chain	LS-85-025	WN
24” Flexible Noodle Retriever	LS-85-120	R24
18” Extendable Pocket Retriever (See page 97)	LS-53-310	LBS

Videos for these products and more are available on YouTube:
Wet Noodle™: <https://youtu.be/EoMMoKI0CF4>