


LEV Series Mechanical Interlocks and Powerswitch® Disconnect Switches with Inform™ Technology



TECHNICAL APPLICATION NOTE ON USAGE WITH VARIABLE FREQUENCY DRIVES (VFDs)

Inform features will function properly


VFD is located between the Mechanical Interlock/Disconnect Switch and the device (drive/motor/etc.)



COMMON APPLICATION:
Portable pump carts typically used in the food and beverage industry

Inform features will not work, however the device will function as normal

VFD is located before the Mechanical Interlock/Disconnect Switch



COMMON APPLICATION:
Multiple VFDs located in a separate area

Learn more at: www.leviton.com/inform • Email: inform@leviton.com