



SF341B Code Call (Code Blue) Station (Supervised)

SF341B CODE CALL STATION



ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

Code Call Station(s) shall be Alpha Communications® / TekTone SF341B or approved equal. Code stations and wiring from code stations to patient stations shall be fully supervised. Operation of emergency signals shall be accomplished by a short pull on the (optional CA015K) nylon cord or (optional CA016K) TPU plastic cord or by pulling/pushing down on the BLUE lever marked "CODE". The RED "CALL PLACED" indicator shall flash to assure that the call has been properly placed. The initiation of the code call shall cause the activation of both audible and visual signals. Call cancellation shall be possible only at point of origination. Reliable, solid-state components shall be used and plug-in connectors shall be provided for electrical connections.

The SF341B shall be UL 1069 Listed to the latest Standards. Contractor shall observe all local and national electrical and building codes.

SF341B CODE CALL STATION

For use in ICU/CCU, physical therapy rooms, post-op recovery, or any location where code call initiation may be required. The SF341B Code Call station is used to operate all system emergency signals. The LARGE 1.5" BLUE pull/push-down lever may be used, or the optional (model CA015K or CA016K) pull cord assembly may be used for code call activation. The call-placed indicator flashes to provide for call assurance. Calls are registered on the master station (and duty station if used) via audible and visual signals pulsing at a rate of twice that of a standard emergency signal. Local indication on dome lights is also provided. Call cancellation is possible only at the originating SF341B location.

FEATURES

- UL 1069 Listed - 4th Edition Standards
- Fully supervised
- Simple and flexible operation
- Registers audible and visual calls at master station
- Indicates local call origination on dome lights
- Call cancellation only at point of origin
- Flame retardant type KJB Cyclocac Plastic
- 1.5" wide Pull-Down lever
- Can be used as a PUSH type station or PULL type (with optional CA015K or CA016K pull cord assembly)

SPECIFICATIONS

Dimensions:	Height: 4.50" (114mm) (less cord) Width: 2.75" (70mm) Depth: 1.63" (41mm) Projects: 0.69" (17mm) from mounting surface (including BLUE pull down lever)
Connection:	Plug-in connectors for all wiring.
Construction:	Electronic components and reed switch, circuit board mounted
Mounting:	Steel City #52171 box with Steel City #52C14 plaster ring, or Alpha Communications® Model #IH358 box with IH357 ring, or EXACT EQUAL. Vertical mount.

